

## Anneau de support jack modulaire 2x Anneau de support MJ-01 à MJ-10



| Spécification                                                                                               | Réf.    | UV.  | EUR/pièce HTVA | SP | EAN           |
|-------------------------------------------------------------------------------------------------------------|---------|------|----------------|----|---------------|
|  Anneau de support MJ-01   | 5601 00 | 1/10 | 7,55           | 01 | 4010337460015 |
|  Anneau de support MJ-02 | 5602 00 | 1/10 | 7,55           | 01 | 4010337460022 |
|  Anneau de support MJ-03 | 5603 00 | 1/10 | 7,55           | 01 | 4010337460039 |
|  Anneau de support MJ-04 | 5604 00 | 1/10 | 7,55           | 01 | 4010337460046 |
|  Anneau de support MJ-05 | 5605 00 | 1/10 | 7,55           | 01 | 4010337460053 |
|  Anneau de support MJ-06 | 5606 00 | 1/10 | 7,55           | 01 | 4010337460060 |
|  Anneau de support MJ-07 | 5607 00 | 1/10 | 7,55           | 01 | 4010337460077 |
|  Anneau de support MJ-08 | 5608 00 | 1/10 | 7,55           | 01 | 4010337460084 |
|  Anneau de support MJ-09 | 5609 00 | 1/10 | 7,55           | 01 | 4010337460091 |



Anneau de support MJ-10

5610 00

1/10

7,55

01

4010337460107

---

## Caractéristiques techniques

### Dimensions

- |                       |                    |
|-----------------------|--------------------|
| - MJ-01, MJ02, MJ-07: | I 14,8 x 19,5 mm   |
| - MJ-03:              | I 14,8 x H 20,0 mm |
| - MJ-04, MJ-09:       | I 14,8 x 19,3 mm   |
| - MJ-05:              | I 16,7 x H 17,3 mm |
| - MJ-06:              | B 15,9 x H 18,3 mm |
| - MJ-08:              | I 14,8 x H 19,0 mm |
| - MJ-10:              | I 16,1 x H 18,5 mm |

---

## Indications

- Uniquement pour fixation par vis.
  - Convient pour l'installation en goulotte.
-