

Cadre de finition Gira E2 blanc brillant



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 1x	0211 29	1/10/100	7,77	01	4010337211297
 1,5x	1001 29	1/10	11,50	01	4010337881353
 2x	0212 29	1/10/100	10,67	01	4010337212294
 2x sans nervure centrale	1002 29	1/10	10,67	01	4010337001553
 3x	0213 29	1/5	19,47	01	4010337213291
 4x	0214 29	1/5	31,45	01	4010337214298
 5x	0215 29	1/5	47,99	01	4010337215295

Caractéristiques

- Plastique : thermoplastique sans halogène, résistant aux chocs, ou alors on parle de polycarbonate.

Indications

- Convient également pour installations en goulotte.
 - En combinaison avec le kit d'étanchéité, le cadre de finition (1 à 5x) convient également pour le montage encastré protégé contre l'eau IP44.
-