








Cadre de finition Gira F200 gris mat (laqué)



| Spécification | Réf. | UV. | EUR/pièce HTVA | SP | EAN |
|--|---------|------|----------------|----|---------------|
|  1x | 0211 76 | 1/10 | 12,63 | 11 | 4010337113164 |
|  2x | 0212 76 | 1/10 | 22,23 | 11 | 4010337113218 |
|  2x sans nervure centrale | 1002 76 | 1/10 | 22,23 | 11 | 4010337113423 |
|  3x | 0213 76 | 1/5 | 34,22 | 11 | 4010337113263 |
|  4x | 0214 76 | 1/5 | 55,43 | 11 | 4010337113324 |
|  5x | 0215 76 | 1/5 | 84,41 | 11 | 4010337113379 |

Caractéristiques

- Dans la version blanc pur brillant : composé à 85 % de plastique bio-circulaire.

Caractéristiques techniques

| | |
|------------------------|---------------------------|
| Cadre de fin. 1x: | B 90,0 x H 90,0 x T 11,4 |
| Cadre de fin. 2x: | B 90,0 x H 161,1 x T 11,4 |
| Cadre de fin. 2x s/NC: | B 90,0 x H 161,1 x T 11,4 |

| | |
|---|---------------------------|
| Cadre de fin. 3x: | B 90,0 x H 232,6 x T 11,4 |
| Cadre de fin. 4x: | B 90,0 x H 303,9 x T 11,4 |
| Cadre de fin. 5x: | B 90,0 x H 375,2 x T 11,4 |
| Rayon d'angle: | R 0,3 |
| Plastique biocirculaire - Version: blanc brillant: | min. 50% |
