

Cadre de finition Gira F300 blanc brillant



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 1x	0211 80	1/10	7,77	01	4010337113478
 2x	0212 80	1/10	10,67	01	4010337113539
 2x sans nervure centrale	1002 80	1/10	10,67	01	4010337131830
 3x	0213 80	1/5	19,47	01	4010337113584
 4x	0214 80	1/5	31,45	01	4010337113638
 5x	0215 80	1/5	47,99	01	4010337131823

Caractéristiques

- Dans la version blanc pur brillant : composé à 85 % de plastique bio-circulaire.

Caractéristiques techniques

Cadre de fin. 1x:	B 80,8 x H 80,8 x T 11,4
Cadre de fin. 2x:	B 80,8 x H 151,9 x T 11,4
Cadre de fin. 2x s/NC:	B 80,8 x H 151,9 x T 11,4

Cadre de fin. 3x:	B 80,8 x H 223,4 x T 11,4
Cadre de fin. 4x:	B 80,8 x H 297,7 x T 11,4
Cadre de fin. 5x:	B 80,8 x H 366,0 x T 11,4
Rayon d'angle:	R 0,5
Plastique biocirculaire - Version: blanc brillant:	min. 50%
