







## Cadre de finition Gira F300 noir mat (laqué)



| Spécification  | Réf.    | UV.  | EUR/pièce HTVA | SP | EAN           |
|--|---------|------|----------------|----|---------------|
|  1x                         | 0211 84 | 1/10 | 12,60          | 11 | 4010337113508 |
|  2x                       | 0212 84 | 1/10 | 19,13          | 11 | 4010337113553 |
|  2x sans nervure centrale | 1002 84 | 1/10 | 19,13          | 11 | 4010337131892 |
|  3x                       | 0213 84 | 1/5  | 31,46          | 11 | 4010337113607 |
|  4x                       | 0214 84 | 1/5  | 51,10          | 11 | 4010337113652 |
|  5x                       | 0215 84 | 1/5  | 77,75          | 11 | 4010337131885 |

### Caractéristiques

- Dans la version blanc pur brillant : composé à 85 % de plastique bio-circulaire.

### Caractéristiques techniques

|                        |                           |
|------------------------|---------------------------|
| Cadre de fin. 1x:      | B 80,8 x H 80,8 x T 11,4  |
| Cadre de fin. 2x:      | B 80,8 x H 151,9 x T 11,4 |
| Cadre de fin. 2x s/NC: | B 80,8 x H 151,9 x T 11,4 |

|   |                           |
|---|---------------------------|
| Cadre de fin. 3x:                                     | B 80,8 x H 223,4 x T 11,4 |
| Cadre de fin. 4x:                                     | B 80,8 x H 297,7 x T 11,4 |
| Cadre de fin. 5x:                                     | B 80,8 x H 366,0 x T 11,4 |
| Rayon d'angle:  | R 0,5                     |
| Plastique biocirculaire<br>- Version: blanc brillant: | min. 50%                  |

---