

## Cadre de finition Gira F200 blanc brillant



| Spécification                                                                                                | Réf.    | UV.  | EUR/pièce HTVA | SP | EAN           |
|--------------------------------------------------------------------------------------------------------------|---------|------|----------------|----|---------------|
|  1x                         | 0211 70 | 1/10 | 7,80           | 01 | 4010337113171 |
|  2x                       | 0212 70 | 1/10 | 13,77          | 01 | 4010337113225 |
|  2x sans nervure centrale | 1002 70 | 1/10 | 13,77          | 01 | 4010337113430 |
|  3x                       | 0213 70 | 1/5  | 22,23          | 01 | 4010337113270 |
|  4x                       | 0214 70 | 1/5  | 35,78          | 01 | 4010337113331 |
|  5x                       | 0215 70 | 1/5  | 54,65          | 01 | 4010337113386 |

### Caractéristiques

- Dans la version blanc pur brillant : composé à 85 % de plastique bio-circulaire.

### Caractéristiques techniques

|                        |                           |
|------------------------|---------------------------|
| Cadre de fin. 1x:      | B 90,0 x H 90,0 x T 11,4  |
| Cadre de fin. 2x:      | B 90,0 x H 161,1 x T 11,4 |
| Cadre de fin. 2x s/NC: | B 90,0 x H 161,1 x T 11,4 |

|                                                       |                           |
|-------------------------------------------------------|---------------------------|
| Cadre de fin. 3x:                                     | B 90,0 x H 232,6 x T 11,4 |
| Cadre de fin. 4x:                                     | B 90,0 x H 303,9 x T 11,4 |
| Cadre de fin. 5x:                                     | B 90,0 x H 375,2 x T 11,4 |
| Rayon d'angle:                                        | R 0,3                     |
| Plastique biocirculaire<br>- Version: blanc brillant: | min. 50%                  |

---