

Cadre de finition Gira F200 blanc satiné (laqué)



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 1x	0211 72	1/10	12,63	11	4010337113188
 2x	0212 72	1/10	22,23	11	4010337113232
 2x sans nervure centrale	1002 72	1/10	22,23	11	4010337113447
 3x	0213 72	1/5	34,22	11	4010337113287
 4x	0214 72	1/5	55,43	11	4010337113348
 5x	0215 72	1/5	84,41	11	4010337113393

Caractéristiques techniques

Cadre de fin. 1x:	B 90,0 x H 90,0 x T 11,4
Cadre de fin. 2x:	B 90,0 x H 161,1 x T 11,4
Cadre de fin. 2x s/NC:	B 90,0 x H 161,1 x T 11,4
Cadre de fin. 3x:	B 90,0 x H 232,6 x T 11,4
Cadre de fin. 4x:	B 90,0 x H 303,9 x T 11,4
Cadre de fin. 5x:	B 90,0 x H 375,2 x T 11,4
Rayon d'angle:	R 0,3

