

Cadre de finition Gira F100 noir mat (laqué)



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 1x	0211 174	1/10	12,60	11	4010337135968
 2x	0212 174	1/10	19,13	11	4010337133612
 2x sans nervure centrale	1002 174	1/10	19,13	11	4010337133650
 3x	0213 174	1/5	31,46	11	4010337133629
 4x	0214 174	1/5	51,10	11	4010337133636
 5x	0215 174	1/5	77,75	11	4010337135845

Caractéristiques techniques

Cadre de fin. 1x:	B 83,3 x H 83,3 x T 10,6
Cadre de fin. 2x:	B 83,3 x H 154,4 x T 10,6
Cadre de fin. 2x s/NC:	B 83,3 x H 154,4 x T 10,6
Cadre de fin. 3x:	B 83,3 x H 225,9 x T 10,6
Cadre de fin. 4x:	B 83,3 x H 297,2 x T 10,6
Cadre de fin. 5x:	B 83,3 x H 368,5 x T 10,6
Rayon d'angle:	R 3

