







## Cadre de finition Gira E1 anthracite



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 1x	0211 152	1/10	8,16	11	4010337125969
 2x	0212 152	1/10	11,79	11	4010337125976
 2x sans nervure centrale	1002 152	1	11,79	11	4010337125983
 3x	0213 152	1/5	20,42	11	4010337125990
 4x	0214 152	1/5	32,89	11	4010337126027
 5x	0215 152	1/5	50,15	11	4010337126041

### Caractéristiques

- Incassable.

### Indications

- Convient également pour installations en goulotte.  
- En combinaison avec le kit d'étanchéité, le cadre de finition (1 à 5x) convient également pour le montage encastré protégé contre l'eau IP44.