







## Cadre de finition Gira E1 blanc satiné



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 1x	0211 151	1/10	7,77	01	4010337126171
 2x	0212 151	1/10	10,67	01	4010337126188
 2x sans nervure centrale	1002 151	1	10,67	01	4010337126195
 3x	0213 151	1/5	19,47	01	4010337126218
 4x	0214 151	1/5	31,45	01	4010337126225
 5x	0215 151	1/5	47,99	01	4010337126232

### Caractéristiques

- Incassable.

### Indications

- Convient également pour installations en goulotte.
- En combinaison avec le kit d'étanchéité, le cadre de finition (1 à 5x) convient également pour le montage encastré protégé contre l'eau IP44.