

Cadre de finition Gira E2 teinte alu (laqué)



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 1x	0211 25	1/10/100	12,60	11	4010337211259
 1,5x	1001 25	1/10	18,64	11	4010337881346
 2x	0212 25	1/10	19,13	11	4010337212256
 2x sans nervure centrale	1002 25	1/10	19,13	11	4010337002253
 3x	0213 25	1/5	31,46	11	4010337213253
 4x	0214 25	1/5	51,10	11	4010337214250
 5x	0215 25	1/5	77,75	11	4010337215257

Caractéristiques

- Plastique : thermoplastique sans halogène, résistant aux chocs, ou alors on parle de polycarbonate.

Indications

- Convient également pour installations en goulotte.
 - En combinaison avec le kit d'étanchéité, le cadre de finition (1 à 5x) convient également pour le montage encastré protégé contre l'eau IP44.
-