








Cadre de finition Gira E2



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 1x	0211 33	1/10	19,86	11	4010337019794
 2x	0212 33	1/10	30,78	11	4010337019800
 2x sans nervure centrale	1002 33	1/10	30,78	11	4010337019848
 3x	0213 33	1/5	56,58	11	4010337019817
 4x	0214 33	1/5	87,80	11	4010337019824
 5x	0215 33	1/5	133,72	11	4010337019831

Indications

- Convient également pour installations en goulotte.
- En combinaison avec le kit d'étanchéité, le cadre de finition (1 à 5x) convient également pour le montage encastré protégé contre l'eau IP44.