










## Ancien - Bascule avec symbole Sonnette



| Spécification  | Réf.     | UV.  | EUR/pièce HTVA | SP | EAN           |
|--|----------|------|----------------|----|---------------|
|  blanc crème brillant | 0286 01  | 1/10 | 6,05           | 01 | 4010337286011 |
|  blanc brillant     | 0286 03  | 1/10 | 6,05           | 01 | 4010337286035 |
|  blanc satiné       | 0286 27  | 1/10 | 6,05           | 01 | 4010337286271 |
|  anthracite         | 0286 28  | 1/10 | 6,58           | 11 | 4010337286288 |
|  teinte alu         | 0286 26  | 1/10 | 9,95           | 11 | 4010337286264 |
|  noir mat           | 0286 005 | 1/10 | 9,95           | 11 | 4010337038252 |
|  gris mat           | 0286 015 | 1/10 | 9,95           | 11 | 4010337079415 |
|  acier inoxydable   | 0286 600 | 1    | 17,56          | 11 | 4010337021698 |

## Indications

- A condition que la livraison soit possible.

---