









## Ancien - Bascule avec symbole Porte



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc crème brillant	0287 01	1/10	6,05	01	4010337287018
 blanc brillant	0287 03	1/10	6,05	01	4010337287032
 blanc satiné	0287 27	1/10	6,05	01	4010337287278
 anthracite	0287 28	1	6,58	11	4010337287285
 teinte alu	0287 26	1	9,95	11	4010337287261
 noir mat	0287 005	1	9,95	11	4010337038283
 gris mat	0287 015	1	9,95	11	4010337079637
 acier inoxydable	0287 600	1	17,56	11	4010337021704

## Indications

- A condition que la livraison soit possible.

---