









Ancien - Bascule 2x avec symbole de flèche



| Spécification | Réf. | UV. | EUR/pièce HTVA | SP | EAN |
|--|----------|------|----------------|----|---------------|
|  blanc crème brillant | 0294 01 | 1/10 | 11,25 | 01 | 4010337294016 |
|  blanc brillant | 0294 03 | 1/10 | 11,25 | 01 | 4010337294030 |
|  blanc satiné | 0294 27 | 1/10 | 11,25 | 01 | 4010337294276 |
|  anthracite | 0294 28 | 1/10 | 11,84 | 11 | 4010337294283 |
|  teinte alu | 0294 26 | 1/10 | 15,26 | 11 | 4010337294269 |
|  noir mat | 0294 005 | 1/10 | 15,73 | 11 | 4010337038108 |
|  gris mat | 0294 015 | 1/10 | 15,73 | 11 | 4010337080206 |
|  acier inoxydable | 0294 600 | 1/10 | 22,79 | 11 | 4010337021735 |

Indications

- A condition que la livraison soit possible.
