









Ancien - Bascule avec zone d'inscription



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc crème brillant	0299 01	1/10	8,54	01	4010337299011
 blanc brillant	0299 03	1/10	8,54	01	4010337299035
 blanc satiné	0299 27	1/10	8,54	01	4010337299271
 anthracite	0299 28	1/10	9,08	11	4010337299288
 teinte alu	0299 26	1	12,46	11	4010337299264
 noir mat	0299 005	1	12,46	11	4010337038122
 gris mat	0299 015	1	12,46	11	4010337080718
 acier inoxydable	0299 600	1	20,04	11	4010337021711

Indications

- A condition que la livraison soit possible.
-

Etendue de la livraison

- Étiquette vierge fournie.
 - Les étiquettes avec les symboles « lumière », « sonnette » et « porte » sont fournies.
-