









Cache avec bouton pour variateur et potentiomètre électronique



| Spécification | Réf. | UV. | EUR/pièce HTVA | SP | EAN |
|--|----------|----------|----------------|----|---------------|
|  blanc crème brillant | 0650 01 | 1/10/100 | 7,20 | 02 | 4010337650010 |
|  blanc brillant | 0650 03 | 1/10/100 | 7,20 | 02 | 4010337650034 |
|  blanc satiné | 0650 27 | 1/10 | 7,20 | 02 | 4010337650270 |
|  anthracite | 0650 28 | 1/10 | 10,81 | 02 | 4010337650287 |
|  teinte alu | 0650 26 | 1/10 | 16,42 | 02 | 4010337650263 |
|  noir mat | 0650 005 | 1/10 | 16,42 | 02 | 4010337036593 |
|  gris mat | 0650 015 | 1/10 | 16,42 | 02 | 4010337081210 |
|  acier inoxydable | 0650 600 | 1 | 22,97 | 02 | 4010337022329 |