









## Cache avec bouton pour variateur et potentiomètre électronique



| Spécification  | Réf.     | UV.      | EUR/pièce HTVA | SP | EAN           |
|--|----------|----------|----------------|----|---------------|
|  blanc crème brillant | 0650 01  | 1/10/100 | 7,20           | 02 | 4010337650010 |
|  blanc brillant     | 0650 03  | 1/10/100 | 7,20           | 02 | 4010337650034 |
|  blanc satiné       | 0650 27  | 1/10     | 7,20           | 02 | 4010337650270 |
|  anthracite         | 0650 28  | 1/10     | 10,81          | 02 | 4010337650287 |
|  teinte alu         | 0650 26  | 1/10     | 16,42          | 02 | 4010337650263 |
|  noir mat           | 0650 005 | 1/10     | 16,42          | 02 | 4010337036593 |
|  gris mat           | 0650 015 | 1/10     | 16,42          | 02 | 4010337081210 |
|  acier inoxydable   | 0650 600 | 1        | 22,97          | 02 | 4010337022329 |