








## Cadre de finition Gira E2 noir mat



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 1x	0211 09	1/10	12,60	11	4010337036739
 1,5x	1001 09	1/10	18,64	11	4010337072775
 2x	0212 09	1/10	19,13	11	4010337036760
 2x sans nervure centrale	1002 09	1/10	19,13	11	4010337036784
 3x	0213 09	1/5	31,46	11	4010337036821
 4x	0214 09	1/5	51,10	11	4010337036869
 5x	0215 09	1/5	77,75	11	4010337036906

### Caractéristiques

- Plastique : thermoplastique sans halogène, résistant aux chocs, ou alors on parle de polycarbonate.

## Indications

- Convient également pour installations en goulotte.
  - En combinaison avec le kit d'étanchéité, le cadre de finition (1 à 5x) convient également pour le montage encastré protégé contre l'eau IP44.
-