

Cadre de finition Gira Standard 55 blanc satiné



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 1x	0211 04	1/10/100	3,21	21	4010337211044
 1,5x	1001 04	1/10	4,33	01	4010337881315
 2x	0212 04	1/10/100	5,48	21	4010337212041
 2x sans nervure centrale	1002 04	1/10	4,05	01	4010337002048
 3x	0213 04	1/10/100	9,66	01	4010337213048
 4x	0214 04	1/5	16,71	01	4010337214045
 5x	0215 04	1/5	27,49	01	4010337215042

Caractéristiques

- Plastique : thermoplastique sans halogène, résistant aux chocs, ou alors on parle de polycarbonate.

Indications

- Convient également pour installations en goulotte.
 - En combinaison avec le kit d'étanchéité, le cadre de finition (1 à 5x) convient également pour le montage encastré protégé contre l'eau IP44.
-