







## Cadre de finition Gira F100 gris mat (laqué)



| Spécification  | Réf.     | UV.  | EUR/pièce HTVA | SP | EAN           |
|--|----------|------|----------------|----|---------------|
|  1x                         | 0211 176 | 1/10 | 12,60          | 11 | 4010337136026 |
|  2x                       | 0212 176 | 1/10 | 19,13          | 11 | 4010337133667 |
|  2x sans nervure centrale | 1002 176 | 1/10 | 19,13          | 11 | 4010337133704 |
|  3x                       | 0213 176 | 1/5  | 31,46          | 11 | 4010337133674 |
|  4x                       | 0214 176 | 1/5  | 51,10          | 11 | 4010337133681 |
|  5x                       | 0215 176 | 1/5  | 77,75          | 11 | 4010337135852 |

### Caractéristiques

- Dans la version blanc pur brillant : composé à 85 % de plastique bio-circulaire.

### Caractéristiques techniques

|                        |                           |
|------------------------|---------------------------|
| Cadre de fin. 1x:      | B 83,3 x H 83,3 x T 10,6  |
| Cadre de fin. 2x:      | B 83,3 x H 154,4 x T 10,6 |
| Cadre de fin. 2x s/NC: | B 83,3 x H 154,4 x T 10,6 |

|   |                           |
|---|---------------------------|
| Cadre de fin. 3x:                                     | B 83,3 x H 225,9 x T 10,6 |
| Cadre de fin. 4x:                                     | B 83,3 x H 297,2 x T 10,6 |
| Cadre de fin. 5x:                                     | B 83,3 x H 368,5 x T 10,6 |
| Rayon d'angle:  | R 3                       |
| Plastique biocirculaire<br>- Version: blanc brillant: | min. 50%                  |

---