







## Cadre de finition Gira E3 Soft touch gris avec cadre de support anthracite



| Spécification  | Réf.     | UV.  | EUR/pièce HTVA | SP | EAN           |
|--|----------|------|----------------|----|---------------|
|  1x                         | 0211 422 | 1/10 | 20,45          | 11 | 4010337023951 |
|  2x                       | 0212 422 | 1/10 | 28,02          | 11 | 4010337023968 |
|  2x sans nervure centrale | 1002 422 | 1/10 | 28,02          | 11 | 4010337024019 |
|  3x                       | 0213 422 | 1/5  | 51,11          | 11 | 4010337023975 |
|  4x                       | 0214 422 | 1/5  | 77,73          | 11 | 4010337023982 |
|  5x                       | 0215 422 | 1/5  | 112,46         | 11 | 4010337023999 |

### Caractéristiques

- Incassable.

### Indications

- Surface soft touch.