



## Entrée de tube M20



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc brillant	1059 03	1/5	1,04	01	4010337109402
 noir mat	1059 005	1/5	6,17	11	4010337109235