










Haut-parleur radio IP encastrée System 55



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc crème brillant	2282 01	1	28,44	03	4010337076230
 blanc brillant	2282 03	1	28,44	03	4010337076247
 blanc satiné	2282 27	1	28,44	03	4010337076254
 anthracite	2282 28	1	30,62	03	4010337076261
 teinte alu	2282 26	1	33,36	03	4010337076162
 noir mat	2282 005	1	33,36	03	4010337037286
 gris mat	2282 015	1	33,36	03	4010337083931
 acier inoxydable	2282 600	1	38,28	03	4010337032861

Caractéristiques

- Haut-parleurs pour le raccordement à la radio encastrée Gira.

Caractéristiques techniques

Profondeur de montage:	32 mm
section de raccordement	
- Raccordement haut-parleur/AUX:	1,5mm ²
Impédance:	8 Ω
Température ambiante:	-5°C à +50°C
