

## Haut-parleur radio IP encastrée



| Spécification                                                                                             | Réf.     | UV. | EUR/pièce HTVA | SP | EAN           |
|-----------------------------------------------------------------------------------------------------------|----------|-----|----------------|----|---------------|
|  blanc crème brillant    | 2282 01  | 1   | 28,44          | 03 | 4010337076230 |
|  blanc brillant        | 2282 03  | 1   | 28,44          | 03 | 4010337076247 |
|  blanc satiné          | 2282 27  | 1   | 28,44          | 03 | 4010337076254 |
|  anthracite            | 2282 28  | 1   | 30,62          | 03 | 4010337076261 |
|  teinte alu (laqué)    | 2282 26  | 1   | 33,36          | 03 | 4010337076162 |
|  noir mat (laqué)      | 2282 005 | 1   | 33,36          | 03 | 4010337037286 |
|  gris mat (laqué)      | 2282 015 | 1   | 33,36          | 03 | 4010337083931 |
|  acier inoxydable      | 2282 600 | 1   | 38,28          | 03 | 4010337032861 |
|  en optique verre noir | 2282 05  | 1   | 38,28          | 03 | 4010337889182 |

## Caractéristiques

- Haut-parleurs pour le raccordement à la radio encastrée Gira.

---

## Caractéristiques techniques

|                                  |                    |
|----------------------------------|--------------------|
| Profondeur de montage:           | 32 mm              |
| section de raccordement          |                    |
| - Raccordement haut-parleur/AUX: | 1,5mm <sup>2</sup> |
| Impédance:                       | 8 $\Omega$         |
| Température ambiante:            | -5°C à +50°C       |

---