









Cache avec sortie oblique 30° et zone d'inscription pour anneau de support jack modulaire 2x



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc crème brillant	2640 01	1/10	8,89	01	4010337460114
 blanc brillant	2640 03	1/10	8,89	01	4010337460138
 blanc satiné	2640 27	1/10	8,89	01	4010337460183
 anthracite	2640 28	1/10	11,73	11	4010337460190
 teinte alu	2640 26	1/10	16,02	11	4010337460176
 noir mat	2640 005	1/10	16,02	11	4010337036500
 gris mat	2640 015	1/10	16,02	11	4010337085195
 acier inoxydable	2640 600	1/10	20,17	11	4010337021582

## Etendue de la livraison

- Étiquette vierge fournie.

---