








Prise British Standard (BS 1363) 13 A 250 V~ avec shutter System 55



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc crème brillant	2776 01	1/10	18,74	29	4010337079347
 blanc brillant	2776 03	1/10	18,74	29	4010337079354
 anthracite	2776 28	1/10	21,46	29	4010337079378
 teinte alu	2776 26	1/10	25,65	29	4010337079361
 noir mat	2776 005	1/10	25,65	29	4010337037774
 gris mat	2776 015	1/10	25,65	29	4010337086352
 acier inoxydable (laqué)	2776 600	1/10	29,48	29	4010337022077

Caractéristiques

- Avec bornes vissées.

Caractéristiques techniques

Profondeur de montage: 17 mm

Indications

- Uniquement pour fixation par vis.
 - Autres fonctions et variantes également disponibles sur demande pour le boîtier BS de 80.
-