

Prise British Standard (BS 1363) 13 A 250 V~ branchée, avec shutter System 55



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc crème brillant	2778 01	1/10	21,64	29	4010337079477
 blanc brillant	2778 03	1/10	21,64	29	4010337079484
 blanc satiné	2778 27	1/10	21,64	29	4010337036418
 anthracite	2778 28	1/10	24,35	29	4010337079507
 teinte alu (laqué)	2778 26	1/10	28,53	29	4010337079491
 noir mat (laqué)	2778 005	1/10	28,53	29	4010337037750
 gris mat (laqué)	2778 015	1/10	28,53	29	4010337086390
 acier inoxydable (laqué)	2778 600	1/10	32,42	29	4010337022091

Caractéristiques

- Avec bornes vissées.
-

Caractéristiques techniques

Profondeur de montage: 20 mm

Indications

- Uniquement pour fixation par vis.
 - Autres fonctions et variantes également disponibles sur demande pour le boîtier BS de 80.
-