

Interrupteur inverseur universel



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc crème brillant	2832 01	1/10	36,52	29	4010337832010
 blanc brillant	2832 03	1/10	36,52	29	4010337832034
 anthracite	2832 28	1/10	39,25	29	4010337832287
 teinte alu	2832 26	1/10	43,42	29	4010337832263
 noir mat	2832 005	1/10	43,42	11	4010337038528
 gris mat	2832 015	1/10	43,42	11	4010337087120
 acier inoxydable (laqué)	2832 600	1/10	47,29	29	4010337022053

Caractéristiques techniques

Profondeur de montage:	25 mm
section de raccordement - Pour les conducteurs jusqu'à:	2,5mm ²

Indications

- Uniquement pour fixation par vis.
