


## Interrupteur de commande à bascule British Standard (BS EN 60669-1) 20 AX 250 V~ avec bascule Disjoncteur à 2 pôles



| Spécification                                                                                          | Réf.     | UV.  | EUR/pièce HTVA | SP | EAN           |
|--------------------------------------------------------------------------------------------------------|----------|------|----------------|----|---------------|
|  blanc crème brillant | 2834 01  | 1/10 | 46,92          | 29 | 4010337078814 |
|  blanc brillant     | 2834 03  | 1/10 | 46,92          | 29 | 4010337078821 |
|  anthracite         | 2834 28  | 1/10 | 47,43          | 29 | 4010337078845 |
|  teinte alu (laqué) | 2834 26  | 1/10 | 50,54          | 29 | 4010337078838 |
|  noir mat (laqué)   | 2834 005 | 1/10 | 50,54          | 29 | 4010337038573 |
|  gris mat (laqué)   | 2834 015 | 1/10 | 50,54          | 29 | 4010337087137 |
|  acier inoxydable   | 2834 600 | 1/10 | 57,72          | 29 | 4010337022305 |

### Caractéristiques techniques

|                                 |                                                |
|---------------------------------|------------------------------------------------|
| Profondeur de montage:          | 24 mm                                          |
| section de raccordement         |                                                |
| - Pour les conducteurs jusqu'à: | 2 × 4 mm <sup>2</sup> ou 1 × 6 mm <sup>2</sup> |

## Indications

- Uniquement pour fixation par vis.
  - BS EN 60669-1.
-