








Interrupteur de commande à bascule British Standard (BS EN 60669-1) 20 AX 250 V~ avec bascule Disjoncteur à 2 pôles



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc crème brillant	2834 01	1/10	46,92	29	4010337078814
 blanc brillant	2834 03	1/10	46,92	29	4010337078821
 anthracite	2834 28	1/10	47,43	29	4010337078845
 teinte alu	2834 26	1/10	50,54	29	4010337078838
 noir mat	2834 005	1/10	50,54	29	4010337038573
 gris mat	2834 015	1/10	50,54	29	4010337087137
 acier inoxydable	2834 600	1/10	57,72	29	4010337022305

Caractéristiques techniques

Profondeur de montage:	24 mm
section de raccordement	
- Pour les conducteurs jusqu'à:	2 × 4 mm ² ou 1 × 6 mm ²

Indications

- Uniquement pour fixation par vis.
 - BS EN 60669-1.
-