








## Interrupteur à bascule British Standard (BS EN 60669-1) 20 AX 250 V CA avec bascule Disjoncteur à 2 pôles



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc crème brillant	2836 01	1/10	38,99	29	4010337078944
 blanc brillant	2836 03	1/10	38,99	29	4010337078951
 anthracite	2836 28	1/10	39,71	29	4010337078975
 teinte alu	2836 26	1/10	42,87	29	4010337078968
 noir mat	2836 005	1/10	42,87	29	4010337038566
 gris mat	2836 015	1/10	42,87	29	4010337087144
 acier inoxydable	2836 600	1/10	49,81	29	4010337021933

### Caractéristiques techniques

Profondeur de montage:	24 mm
section de raccordement	
- Pour les conducteurs jusqu'à:	2 × 4 mm <sup>2</sup> ou 1 × 6 mm <sup>2</sup>

## Indications

- Uniquement pour fixation par vis.
  - BS EN 60669-1.
-