










## Bascule avec symbole Lumière



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc crème brillant	3285 01	1	6,05	01	4010337039600
 blanc brillant	3285 03	1/10	6,05	01	4010337039617
 blanc satiné	3285 27	1/5	6,05	01	4010337039631
 anthracite	3285 28	1/5	6,58	11	4010337039648
 teinte alu	3285 26	1	9,95	11	4010337039624
 noir mat	3285 005	1/5	9,95	11	4010337067757
 gris mat	3285 015	1	9,95	11	4010337110460
 acier inoxydable	3285 600	1	17,56	11	4010337044994