










Bascule avec symbole Sonnette



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc crème brillant	3286 01	1	6,05	01	4010337039723
 blanc brillant	3286 03	1/10	6,05	01	4010337039730
 blanc satiné	3286 27	1/10	6,05	01	4010337039754
 anthracite	3286 28	1/10	6,58	11	4010337039761
 teinte alu	3286 26	1	9,95	11	4010337039747
 noir mat	3286 005	1/5	9,95	11	4010337067870
 gris mat	3286 015	1	9,95	11	4010337110477
 acier inoxydable	3286 600	1	17,56	11	4010337045151