










Bascule avec symbole Sonnette



| Spécification | Réf. | UV. | EUR/pièce HTVA | SP | EAN |
|--|----------|------|----------------|----|---------------|
|  blanc crème brillant | 3286 01 | 1 | 6,05 | 01 | 4010337039723 |
|  blanc brillant | 3286 03 | 1/10 | 6,05 | 01 | 4010337039730 |
|  blanc satiné | 3286 27 | 1/10 | 6,05 | 01 | 4010337039754 |
|  anthracite | 3286 28 | 1/10 | 6,58 | 11 | 4010337039761 |
|  teinte alu | 3286 26 | 1 | 9,95 | 11 | 4010337039747 |
|  noir mat | 3286 005 | 1/5 | 9,95 | 11 | 4010337067870 |
|  gris mat | 3286 015 | 1 | 9,95 | 11 | 4010337110477 |
|  acier inoxydable | 3286 600 | 1 | 17,56 | 11 | 4010337045151 |