

## Bascule avec symbole Porte



| Spécification                                                                                          | Réf.     | UV.  | EUR/pièce HTVA | SP | EAN           |
|--------------------------------------------------------------------------------------------------------|----------|------|----------------|----|---------------|
|  blanc crème brillant | 3287 01  | 1    | 6,05           | 01 | 4010337039846 |
|  blanc brillant     | 3287 03  | 1/10 | 6,05           | 01 | 4010337039853 |
|  blanc satiné       | 3287 27  | 1/5  | 6,05           | 01 | 4010337039877 |
|  anthracite         | 3287 28  | 1    | 6,58           | 11 | 4010337039884 |
|  teinte alu (laqué) | 3287 26  | 1    | 9,95           | 11 | 4010337039860 |
|  noir mat (laqué)   | 3287 005 | 1    | 9,95           | 11 | 4010337067931 |
|  gris mat (laqué)   | 3287 015 | 1    | 9,95           | 11 | 4010337110484 |
|  acier inoxydable   | 3287 600 | 1    | 17,56          | 11 | 4010337045250 |