






Bascule avec symbole Porte



| Spécification | Réf. | UV. | EUR/pièce HTVA | SP | EAN |
|--|---------|------|----------------|----|---------------|
|  blanc brillant | 3287 70 | 1/10 | 7,61 | 01 | 4010337119869 |
|  blanc satiné (laqué) | 3287 72 | 1/10 | 11,51 | 11 | 4010337119876 |
|  anthracite (laqué) | 3287 73 | 1/10 | 11,51 | 11 | 4010337119883 |
|  noir mat (laqué) | 3287 74 | 1/10 | 11,51 | 11 | 4010337119906 |
|  gris mat (laqué) | 3287 76 | 1/10 | 11,51 | 11 | 4010337119890 |