






## Bascule 2x avec symbole de flèche



| Spécification  | Réf.    | UV.  | EUR/pièce HTVA | SP | EAN           |
|--|---------|------|----------------|----|---------------|
|  blanc brillant         | 3294 70 | 1/10 | 12,60          | 01 | 4010337118992 |
|  blanc satiné (laqué) | 3294 72 | 1/10 | 16,61          | 11 | 4010337119012 |
|  anthracite (laqué)   | 3294 73 | 1/10 | 16,61          | 11 | 4010337119029 |
|  noir mat (laqué)     | 3294 74 | 1/10 | 16,61          | 11 | 4010337119043 |
|  gris mat (laqué)     | 3294 76 | 1/10 | 16,61          | 11 | 4010337119036 |