









## Bascule 2x



| Spécification  | Réf.     | UV.      | EUR/pièce HTVA | SP | EAN           |
|--|----------|----------|----------------|----|---------------|
|  blanc crème brillant | 3295 01  | 1/10     | 8,21           | 01 | 4010337040811 |
|  blanc brillant     | 3295 03  | 1/10/100 | 8,21           | 01 | 4010337040828 |
|  blanc satiné       | 3295 27  | 1/10     | 8,21           | 01 | 4010337040842 |
|  anthracite         | 3295 28  | 1/10     | 8,81           | 11 | 4010337040859 |
|  teinte alu         | 3295 26  | 1/10     | 12,23          | 11 | 4010337040835 |
|  noir mat           | 3295 005 | 1/10     | 12,23          | 11 | 4010337065616 |
|  gris mat           | 3295 015 | 1/10/100 | 12,23          | 11 | 4010337110514 |
|  acier inoxydable   | 3295 600 | 1/5      | 19,74          | 11 | 4010337045267 |