









Bascule 2x



| Spécification | Réf. | UV. | EUR/pièce HTVA | SP | EAN |
|--|----------|----------|----------------|----|---------------|
|  blanc crème brillant | 3295 01 | 1/10 | 8,21 | 01 | 4010337040811 |
|  blanc brillant | 3295 03 | 1/10/100 | 8,21 | 01 | 4010337040828 |
|  blanc satiné | 3295 27 | 1/10 | 8,21 | 01 | 4010337040842 |
|  anthracite | 3295 28 | 1/10 | 8,81 | 11 | 4010337040859 |
|  teinte alu | 3295 26 | 1/10 | 12,23 | 11 | 4010337040835 |
|  noir mat | 3295 005 | 1/10 | 12,23 | 11 | 4010337065616 |
|  gris mat | 3295 015 | 1/10/100 | 12,23 | 11 | 4010337110514 |
|  acier inoxydable | 3295 600 | 1/5 | 19,74 | 11 | 4010337045267 |