






Bascule 2x avec symboles de flèche



| Spécification | Réf. | UV. | EUR/pièce HTVA | SP | EAN |
|--|---------|------|----------------|----|---------------|
|  blanc brillant | 3297 70 | 1/10 | 12,60 | 01 | 4010337119050 |
|  blanc satiné (laqué) | 3297 72 | 1/10 | 16,61 | 11 | 4010337119067 |
|  anthracite (laqué) | 3297 73 | 1/10 | 16,61 | 11 | 4010337119074 |
|  noir mat (laqué) | 3297 74 | 1/10 | 16,61 | 11 | 4010337119098 |
|  gris mat (laqué) | 3297 76 | 1/10 | 16,61 | 11 | 4010337119081 |