









Bascule avec zone d inscription



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc crème brillant	3299 01	1	8,54	01	4010337039471
 blanc brillant	3299 03	1/10	8,54	01	4010337039488
 blanc satiné	3299 27	1	8,54	01	4010337039501
 anthracite	3299 28	1	9,08	11	4010337039518
 teinte alu	3299 26	1	12,46	11	4010337039495
 noir mat	3299 005	1	12,46	11	4010337066859
 gris mat	3299 015	1	12,46	11	4010337110545
 acier inoxydable	3299 600	1/5	20,04	11	4010337044956

Etendue de la livraison

- Étiquette vierge fournie.
 - Les étiquettes avec les symboles « lumière », « sonnette » et « porte » sont fournies.
-