








## Prise SCHUKO 16 A 250 V~ avec impression «EDV» System 55



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc crème brillant	4458 01	1/5	9,33	01	4010337093176
 blanc brillant	4458 03	1/5	9,33	01	4010337093190
 blanc satiné	4458 27	1/5	9,33	01	4010337093213
 anthracite	4458 28	1/5	10,68	11	4010337093220
 teinte alu	4458 26	1/5	15,52	11	4010337093206
 noir mat	4458 005	1/5	15,52	11	4010337093169
 gris mat	4458 015	1/5	15,52	11	4010337093183

### Caractéristiques techniques

Profondeur de montage:	32 mm
Propriétés des conducteurs:	rigide et flexible
section de raccordement - Pour les conducteurs de:	1,5 mm <sup>2</sup> à 2,5 mm <sup>2</sup>

## Indications

- Contrôlé selon T.N.O. avec pression de compression augmentée de l'étrier de mise à la terre

---