












Jeu de bascules 4x pour Tastsensor 4.95



| Spécification | Réf. | UV. | EUR/pièce HTVA | SP | EAN |
|--|----------|-----|----------------|----|---------------|
|  aluminium blanc brillant (laqué) | 5024 903 | 1 | 163,21 | 06 | 4010337098584 |
|  aluminium blanc satiné (laqué) | 5024 927 | 1 | 163,21 | 06 | 4010337098614 |
|  aluminium anthracite (laqué) | 5024 928 | 1 | 163,21 | 06 | 4010337098522 |
|  aluminium (anodisé) | 5024 17 | 1 | 113,00 | 06 | 4010337072294 |
|  aluminium noir mat (laqué) | 5024 905 | 1 | 163,21 | 06 | 4010337098553 |
|  aluminium gris mat (laqué) | 5024 915 | 1 | 163,21 | 06 | 4010337098492 |
|  aluminium noir (anodisé) | 5024 126 | 1 | 113,00 | 06 | 4010337072096 |
|  Bronze (PVD) | 5024 38 | 1 | 301,33 | 06 | 4010337098645 |
|  verre blanc | 5024 12 | 1 | 113,00 | 06 | 4010337072034 |

| | | | | | | |
|---|------------------|----------|---|--------|----|---------------|
|  | verre noir | 5024 05 | 1 | 113,00 | 06 | 4010337071488 |
|  | acier inoxydable | 5024 219 | 1 | 226,00 | 06 | 4010337072065 |