









Module rapporté de commande System 3000 System 55

Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc crème brillant	5360 01	1/5	28,64	02	4010337027201
 blanc brillant	5360 03	1/5	28,64	02	4010337027218
 blanc satiné	5360 27	1/5	28,64	02	4010337027232
 anthracite	5360 28	1/5	31,63	02	4010337027249
 teinte alu	5360 26	1/5	36,36	02	4010337027225
 noir mat	5360 005	1/5	36,36	02	4010337037453
 gris mat	5360 015	1/5	36,36	02	4010337087205
 acier inoxydable	5360 600	1/5	44,94	02	4010337027256

Caractéristiques techniques

Température ambiante: -20 °C à +45 °C