









Bascule 1x sans impression avec fenêtre de contrôle System 55



| Spécification | Réf. | UV. | EUR/pièce HTVA | SP | EAN |
|--|----------|-----|----------------|----|---------------|
|  • blanc crème brillant | 5371 01 | 1/5 | 6,41 | 02 | 4010337108337 |
|  • blanc brillant | 5371 03 | 1/5 | 6,41 | 02 | 4010337108344 |
|  • blanc satiné | 5371 27 | 1/5 | 6,41 | 02 | 4010337108351 |
|  • anthracite | 5371 28 | 1/5 | 9,64 | 02 | 4010337108368 |
|  • teinte alu | 5371 26 | 1/5 | 11,56 | 02 | 4010337108375 |
|  • noir mat | 5371 005 | 1/5 | 11,56 | 02 | 4010337108382 |
|  • gris mat | 5371 015 | 1/5 | 11,56 | 02 | 4010337108399 |
|  • acier inoxydable | 5371 600 | 1/5 | 17,34 | 02 | 4010337108405 |

Caractéristiques

- Bascule de commande sans inscription en remplacement de la bascule d'origine marquée de symboles.

Indications

- En cas d'utilisation d'un module rapporté en métal et/ou d'un cadre de finition en métal, la portée peut diminuer.
