









## Bascule 1x sans impression avec fenêtre de contrôle System 55



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 • blanc crème brillant	5371 01	1/5	6,41	02	4010337108337
 • blanc brillant	5371 03	1/5	6,41	02	4010337108344
 • blanc satiné	5371 27	1/5	6,41	02	4010337108351
 • anthracite	5371 28	1/5	9,64	02	4010337108368
 • teinte alu	5371 26	1/5	11,56	02	4010337108375
 • noir mat	5371 005	1/5	11,56	02	4010337108382
 • gris mat	5371 015	1/5	11,56	02	4010337108399
 • acier inoxydable	5371 600	1/5	17,34	02	4010337108405

## Caractéristiques

- Bascule de commande sans inscription en remplacement de la bascule d'origine marquée de symboles.

---

## Indications

- En cas d'utilisation d'un module rapporté en métal et/ou d'un cadre de finition en métal, la portée peut diminuer.

---