

Bascule 2x avec symboles de flèche et fenêtre de contrôle System 55



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc crème brillant	5386 01	1/5	13,88	02	4010337111672
 blanc brillant	5386 03	1/5	13,88	02	4010337111689
 blanc satiné	5386 27	1/5	13,88	02	4010337111696
 anthracite	5386 28	1/5	16,83	02	4010337111702
 teinte alu	5386 26	1/5	18,89	02	4010337111719
 noir mat	5386 005	1/5	18,89	02	4010337111726
 gris mat	5386 015	1/5	18,89	02	4010337111733
 acier inoxydable	5386 600	1/5	22,48	02	4010337111740

Caractéristiques

- Toutes utilisables de manière universelle pour la bascule de gauche et de droite.
-

Indications

- En cas d'utilisation d'un module rapporté en métal et/ou d'un cadre de finition en métal, la portée peut diminuer.
-