

Anneau de support jack modulaire 2x Anneau de support MJ-01 à MJ-10



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 Anneau de support MJ-01	5601 00	1/10	7,55	01	4010337460015
 Anneau de support MJ-02	5602 00	1/10	7,55	01	4010337460022
 Anneau de support MJ-03	5603 00	1/10	7,55	01	4010337460039
 Anneau de support MJ-04	5604 00	1/10	7,55	01	4010337460046
 Anneau de support MJ-05	5605 00	1/10	7,55	01	4010337460053
 Anneau de support MJ-06	5606 00	1/10	7,55	01	4010337460060
 Anneau de support MJ-07	5607 00	1/10	7,55	01	4010337460077
 Anneau de support MJ-08	5608 00	1/10	7,55	01	4010337460084
 Anneau de support MJ-09	5609 00	1/10	7,55	01	4010337460091



Anneau de support MJ-10

5610 00

1/10

7,55

01

4010337460107

Caractéristiques techniques

Dimensions

- | | |
|-----------------------|--------------------|
| - MJ-01, MJ02, MJ-07: | I 14,8 x 19,5 mm |
| - MJ-03: | I 14,8 x H 20,0 mm |
| - MJ-04, MJ-09: | I 14,8 x 19,3 mm |
| - MJ-05: | I 16,7 x H 17,3 mm |
| - MJ-06: | B 15,9 x H 18,3 mm |
| - MJ-08: | I 14,8 x H 19,0 mm |
| - MJ-10: | I 16,1 x H 18,5 mm |

Indications

- Uniquement pour fixation par vis.
 - Convient pour l'installation en goulotte.
-