







Placca Gira F100 bianco puro satinato (verniciato)



| Specifica | Cod. ord. | UI | EUR/pezzo IVA esclusa | SP | EAN |
|---------------------------------------------------------------------------------------------------------------------|-----------|------|-----------------------|----|---------------|
|  1 modulo | 0211 172 | 1/10 | 12,60 | 11 | 4010337133506 |
|  2 moduli | 0212 172 | 1/10 | 19,13 | 11 | 4010337133513 |
|  2 moduli senza costola centrale | 1002 172 | 1/10 | 19,13 | 11 | 4010337133551 |
|  3 moduli | 0213 172 | 1/5 | 31,46 | 11 | 4010337133520 |
|  4 moduli | 0214 172 | 1/5 | 51,10 | 11 | 4010337133537 |
|  5 moduli | 0215 172 | 1/5 | 77,75 | 11 | 4010337133544 |

Caratteristiche

- Nella versione di colore bianco puro lucido: realizzato con l'85% di plastica bio-circolare.

Dati tecnici

| | |
|-------------------|---------------------------|
| Placca 1-m: | B 83,3 x H 83,3 x T 10,6 |
| Placca 2-m: | B 83,3 x H 154,4 x T 10,6 |
| Placca 2-m s/COC: | B 83,3 x H 154,4 x T 10,6 |

| | |
|-----------------------------------------------------------------------|---------------------------|
| Placca 3-m: | B 83,3 x H 225,9 x T 10,6 |
| Placca 4-m: | B 83,3 x H 297,2 x T 10,6 |
| Placca 5-m: | B 83,3 x H 368,5 x T 10,6 |
| Raggio angolare: | R 3 |
| Plastica biocircolare - Versione di colore: bianco puro brillante: | min. 50% |
